



1 Anti-Slip_ShowerTray_Senstec_Rectangular Plan

Detailed Description
 Senstec Anti-Slip shower trays have a unique integrated profile that has been designed to not only increase grip levels, but is also comfortable to stand on and is easily cleaned. EN 14527 Class 1. The base of the Tray must be adequately supported.

Anti-slip properties:
 UKAS accredited laboratory results. Pendulum Test, BS 7976_2:2002, With the NON REQUIRED addition of contaminant to reflect a showering environment, PTV value of 48. Ramp Test DIN 51097, Ramp angle of 30 degrees, best category classification of C. Senstec Ant-Slip properties fall into best possible classifications when tested to BS7976_2:2002 and DIN 51097. User Experience testing carried out by University of Ulster showed 94% very positive.

Material:
 Gelcoat surface, stone resin fill.

Depth:
 36 mm.

Colour:
 Available in all colours.

Waste:
 Senstec shower trays have been designed exclusively for use with McAlpine ST90CPB-S-HP2 or ST90CPB-S-70, with flow rates of 42 and 34 litres per minute respectively when tested in accordance with EN274-2:2002. <http://mcalpineplumbing.com>

2 Anti-Slip_ShowerTray_Senstec_Rectangular Tray Size Schedule

(a) mm	(b) mm	(c) mm	(d) mm	(e) mm	(f) mm
1800	1000	990	810	180	820
1800	900	990	810	180	720
1800	800	990	810	180	620
1700	1000	940	760	180	820
1700	900	940	760	180	720
1700	800	940	760	180	620
1700	750	940	760	180	570
1600	1000	890	710	180	820
1600	900	890	710	180	720
1600	800	890	710	180	620
1500	1000	840	660	180	820
1500	900	840	660	180	720
1500	800	840	660	180	620
1400	1000	790	610	180	820
1400	900	790	610	180	720
1400	800	790	610	180	620
1300	900	740	560	180	720
1300	800	740	560	180	620
1200	1000	690	510	180	820
1200	900	690	510	180	720
1200	800	690	510	180	620
1200	760	690	510	180	580
1100	900	640	460	180	720
1100	800	640	460	180	620
1100	760	640	460	180	580
1000	900	590	410	180	720
1000	800	590	410	180	620
1000	760	590	410	180	580
900	800	540	360	180	620
900	760	540	360	180	580

3 Anti-Slip_ShowerTray_Senstec_Rectangular Detailed Description

NOTES:

Waste
 Senstec shower trays have been designed exclusively for use with McAlpine ST90CPB-S-HP2 or ST90CPB-S-70, with flow rates of 42 and 34 litres per minute respectively when tested in accordance with EN274-2:2002. <http://mcalpineplumbing.com>

Waterproofing
 When installing a Senstec Anti-Slip shower tray it is recommended to use the Classi Bathroom Waterproofing range of products <http://waterproofyourbathroom.com/shower-trays>

Cleaning
 Ensure that the tray is washed with soap and water and dried with a soft cloth after each use.

ORIGINAL BY Senstec DATE **10/04/2019**

Contact
 Senstec | 185 Omagh Road | Ballygawley | Dungannon | Co. Tyrone | N.Ireland | BT70 2AL

Drawing Name: Anti-Slip Shower Tray - Senstec Rectangular - Technical Data Sheet
 Drawing Number: SENSTEC-STC-XX-XX-DS-A-20-001
 Drawing Status: Information Rev: P1

THIS DRAWING IS PROPERTY OF SENSTEC AND REMAINS PROPERTY OF SENSTEC. ANY DRAWING DISCREPANCY SHOULD BE NOTIFIED TO THE DRAWING ORIGINATOR IMMEDIATELY. THIS DRAWING SHOULD NOT BE COPIED WITHOUT NOTIFICATION TO THE OWNER. THIS DRAWING IS FOR PLANNING PURPOSES ONLY & NO DIMENSIONS SCALING SHOULD BE USED FOR FABRICATION. ALL DIMENSIONS TO BE MEASURED ON SITE PRIOR TO MANUFACTURE OF ANY PROPOSALS